

MATERIAL COMPARISON CHART

01.07.2025 - Version 5.5

Table 1: Technical Properties

		TECHNICAL PROPERTIES										
		MFI 190°C/2.16 kg (g/10 min)	Flexural strain (%)	Tensile modulus (GPa)	Tensile Strain at yield (%)	HDT-B (°C)	Charpy impact strength (kJ/m²)	Material Density (g/cm³)	Shrinkage (%)	Mold Temperature (°C)	Recommended Minimum object thickness (mm)	Wood chip size
SULAPAC MATERIALS	SULAPAC PREMIUM	N.A	2	4,9	1,2	56	6	1,27	0,2	20 - 40	2	Large
	SULAPAC PREMIUM FLEX 40	N.A	2,1	4,4	1,4	56	7,8	1,27	0,2	20 - 40	2	Large
	SULAPAC UNIVERSAL	12	1,9	4,5	1,6	56	10	1,27	0,2	20 - 40	0,6 - 1	Small
	SULAPAC UNIVERSAL FLEX 30	12	2,7	3,0	2,7	56	12	1,27	0,3	20 - 40	0,6 - 1	Small
	SULAPAC UNIVERSAL FLEX 35	8	3,6	3,8	2,1	56	12	1,27	0,3	20 - 40	0,6	Small
	SULAPAC UNIVERSAL HEAT 30	7	2,9	3,3	2,7	95	8	1,41	0,2	20 - 40	0,6 - 1	Small
	SULAPAC SOLID 2.0	22	1,3	7,8	1,3	135	16	1,4	0,15	>100	0,5	None
	SULAPAC LUXE	14	3	3,2	2,8	54	16	1,27	0,36	20 - 40	0,6 - 1	Fine
	SULAPAC LUXE FLEX	31	6,5	2,3	30	53	19	1,27	0,36	20 - 40	0,6 - 1	None
	SULAPAC BARRIER	12	1,1	8,7	1,1	150	9	1,49	1,0	60 – 70	0,5 - 1	None
	SULAPAC FLOW 1.7	3	4,5	2,1	3	55	33	1,26	N.A	-	0,2	Fine
	SULAPAC FLOW 1.8	3	4,5	2,1	3	54	33	1,26	N.A	-	0,5	Fine
	SULAPAC SOFT	7	>6	0,3	230	-	NB	1,17	0,85	20 - 30	0,6 - 1	None

Table 2: Verified Processing Methods

		VERIFIED PROCESSNG METHODS					
SULAPAC MATERIALS		Injection Molding	Extrusion	Thermoforming	3D Printing		Recommended Minimum Object Thickness (mm)
					Granules	Filament	
	SULAPAC PREMIUM	✓					2
	SULAPAC PREMIUM FLEX 40	✓					2
	SULAPAC UNIVERSAL	✓					0,6 - 1
	SULAPAC UNIVERSAL FLEX 30	✓					0,6 - 1
	SULAPAC UNIVERSAL FLEX 35	✓					0,6
	SULAPAC UNIVERSAL HEAT 30	✓			✓		0,6 - 1
	SULAPAC SOLID 2.0	✓					0,5
	SULAPAC LUXE	✓					0,6 - 1
	SULAPAC LUXE FLEX	✓					0,6 - 1
	SULAPAC BARRIER	✓					0,5 - 1
	SULAPAC FLOW 1.7	✓	✓	✓	✓	✓	0,2
	SULAPAC FLOW 1.8		✓				0,5
	SULAPAC SOFT	✓	✓		✓		0,6 - 1

Table 3: Verified Applications

		VERIFIED APPLICATIONS							
		Cosmetic Jars and Caps	Make-up	Supplement Packaging	Luxury Packaging	Kitchen Ware	Straw	Cutlery	Point of Sale Displays
SULAPAC MATERIALS	SULAPAC PREMIUM	✓		✓	✓				
	SULAPAC PREMIUM FLEX 40	✓			✓				
	SULAPAC UNIVERSAL	✓	✓	✓	✓			✓	
	SULAPAC UNIVERSAL FLEX 30							✓	
	SULAPAC UNIVERSAL FLEX 35	✓		✓	✓				
	SULAPAC UNIVERSAL HEAT 30							✓	
	SULAPAC SOLID 2.0	✓	✓		✓	✓			
	SULAPAC LUXE	✓	✓		✓				
	SULAPAC LUXE FLEX	✓	✓		✓				
	SULAPAC BARRIER	✓*		✓*					
	SULAPAC FLOW 1.7		✓				✓		✓
	SULAPAC FLOW 1.8		✓						
SULAPAC SOFT	✓	✓	✓	✓	✓				

* Inner layer of jar (2k jar or 4-part mold)

Table 4: Key Features

		KEY FEATURES					
		No Permanent Microplastics	Safe For People and The Planet	Sustainably Sourced	Mass Produducible	Industrially Compostable	Bio-Based %
SULAPAC MATERIALS	SULAPAC PREMIUM	✓	✓	✓	✓	✓	100 %
	SULAPAC PREMIUM FLEX 40	✓	✓	✓	✓	✓	87 %
	SULAPAC UNIVERSAL	✓	✓	✓	✓	✓	100 %
	SULAPAC UNIVERSAL FLEX 30	✓	✓	✓	✓	✓	79 %
	SULAPAC UNIVERSAL FLEX 35	✓	✓	✓	✓	✓	87 %
	SULAPAC UNIVERSAL HEAT 30	✓	✓	✓	✓	✓	70 %
	SULAPAC SOLID 2.0	✓	✓	✓	✓	✓	100 %
	SULAPAC LUXE	✓	✓	✓	✓	✓	87 %
	SULAPAC LUXE FLEX	✓	✓	✓	✓	✓	86 %
	SULAPAC BARRIER	✓	✓	✓	✓	✓	98 %
	SULAPAC FLOW 1.7	✓	✓	✓	✓	✓	72 %
	SULAPAC FLOW 1.8	✓	✓	✓	✓	✓	72 %
	SULAPAC SOFT	✓	✓	✓	✓	✓	55 %

Table 5: Material Certificates

MATERIAL CERTIFICATES								
SULAPAC MATERIALS	Industrial Compostability					Bio-Based %	Non-GMO*	Wood
	Self-Declaration	BPI ASTM D6400	Seedling EN 13432 / ASTM D6400	OK Compost Industrial EN 13432	OK Compost Home	BioPreferred ASTM D6866	Self-Declaration	FSC Mix <u>INS-COC-100087</u>
	SULAPAC PREMIUM	✓				100 %	✓	✓
	SULAPAC PREMIUM FLEX 40	✓				87 %	✓	✓
	SULAPAC UNIVERSAL	✓				100 %	✓	
	SULAPAC UNIVERSAL FLEX 30	✓	✓			79 %	✓	
	SULAPAC UNIVERSAL FLEX 35	✓				87 %	✓	
	SULAPAC UNIVERSAL HEAT 30	✓				70 %		
	SULAPAC SOLID 2.0	✓				100 %	✓	
	SULAPAC LUXE	✓				87 %	**	✓
	SULAPAC LUXE FLEX			✓		86 %	**	
	SULAPAC BARRIER	✓				98 %	✓	
	SULAPAC FLOW 1.7	✓	✓			72 %	✓	
	SULAPAC FLOW 1.8	✓	✓			72 %	✓	✓
	SULAPAC SOFT			✓	✓	55 %	✓	

* Virgin raw materials confirmed as non-GMO by manufacturers

** Non-GMO version available upon request